

N18D

● Double carriage

Ordering method

N18D - 20						RCX222HP		R			
Model	Lead designation	Installation direction	Cable carrier specification	Option	Stroke	Cable length	Controller ^{Note 1}	Usable for CE	Regenerative unit	I/O selection1	I/O selection2
		H: Horizontal installation W: Wall installation	S: Standard Cable carrier M: Optional Cable carrier	Grease type None: Standard GC: Clean	250 to 2250 (100mm pitch)	3L: 3.5m (Standard) 5L: 5m 10L: 10m	RCX222HP DRCX-2020 SR1-X (2 units) ^{Note 2} TS-X (2 units) ^{Note 2} RDX (2 units) ^{Note 2}	No entry: Standard E: CE marking	R: RG2 (RCX222HP)	N: NPN ^{Note 3} P: PNP CC: CC-Link DN: DeviceNet PB: Profibus EN: Ethernet ^{Note 3} YC: YC-Link ^{Note 3}	No entry: None N1: OPDIO24/16 (NPN) ^{Note 3} P1: OPDIO24/17 (PNP) EN: Ethernet ^{Note 3}



Note 1. To find controller selection options for other than the RCX222HP, see the ordering method on each controller page (DRCX: P.387, SR1-X: P.377, TS-X: P.355, RDX: P.365).
 Note 2. 2 units are required when using SR1-X, TS-X or RDX.
 Note 3. NPN and Ethernet cannot be selected when using CE marking. Note 4. Available only for the master.
 Note 5. Only when you have selected CC, DN or PB for Input/Output selection 1, you can select EN for Input/Output selection 2.

Specifications

AC servo motor output (W)	400
Repeatability ^{Note 1} (mm)	+/-0.01
Deceleration mechanism	Ball screw $\phi 20$ (Class C7)
Ball screw lead (mm)	20
Maximum speed ^{Note 2} (mm/sec)	1200
Maximum payload (kg)	80
Rated thrust (N)	339
Stroke (mm)	250 to 2250 (100 pitch)
Overall length (mm)	Stroke+362
Maximum dimensions of cross section of main unit (mm)	W180 x H115
Cable length (m)	Standard: 3.5 / Option: 5.10
Linear guide type	4 rows of circular arc grooves x 2 rail
Position detector	Resolvers ^{Note 3}
Resolution (Pulse/rotation)	16384

Note 1. Positioning repeatability in one direction.
 Note 2. The maximum speed may not be reached when the moving distance is short.
 Note 3. Position detectors (resolvers) are common to incremental and absolute specifications. If the controller has a backup function then it will be absolute specifications.


Allowable overhang^{Note}

Horizontal installation (Unit: mm)				Wall installation (Unit: mm)			
Lead 20	A	B	C	Lead 20	A	B	C
30kg	3045	1629	1902	30kg	1928	1553	3045
50kg	2602	961	1150	50kg	1157	885	2602
80kg	2193	586	716	80kg	707	509	2193

Note. Distance from center of slider top to center of gravity of object being carried at a guide service life of 10,000 km.

Static loading moment



(Unit: N-m)		
MY	MP	MR
1161	1163	1021


Controller

Controller	Operation method
RCX222HP-R	Programming / I/O point trace / Remote command / Operation using RS-232C communication
DRCX-2020-R	Operation using RS-232C communication
SR1-X-20-R ^{Note 5}	I/O point trace
TS-X220-R ^{Note 5}	Pulse train control
RDX-20-RB1 ^{Note 5}	


Note. 2 units are required when using SR1-X, TS-X or RDX.

Cable carrier for users

S type Standard cable carrier




M type Optional cable carrier



Note. Cannot pass more than 3 urethane hoses ($\phi 6 \times 4$).
 Space for optional cable for users


N18D: Horizontal installation / Standard Cable carrier specification




Note 1. Position of table carriage when searched to the origin.
 Note 2. Distance from both ends to the mechanical stopper.
 Note 3. When using $\phi 9$ holes for installation, do not use a washer, spring washer, etc. in the main unit.
 Note 4. If the model is a standard cable carrier specification, it is not possible to pass 3 or more $\phi 6 \times 4$ urethane air hoses.
 Note 5. When using a $\phi 10H7$ hole, make sure that the pin does not go into deeper than as shown in the drawing.
 Note 6. Contact us for vertical installation.
 Note 7. For the robot with more than 2,050 stroke, a roller to prevent the cable carrier from hanging is provided.
 Note 8. Weight of models with no brake. The weight of brake-attached models is 1 kg heavier than the models with no brake shown in the table.

Effective stroke	250	350	450	550	650	750	850	950	1050	1150	1250	1350	1450	1550	1650	1750	1850	1950	2050	2150	2250
L	862	962	1062	1162	1262	1362	1462	1562	1662	1762	1862	1962	2062	2162	2262	2362	2462	2562	2662	2762	2862
A	131	81	131	81	131	81	131	81	131	81	131	81	131	81	131	81	131	81	131	81	131
B	3	4	4	5	5	6	6	7	7	8	8	9	9	10	10	11	11	12	12	13	13
C	8	10	10	12	12	14	14	16	16	18	18	20	20	22	22	24	24	26	26	28	28
D	650	750	850	950	1050	1150	1250	1350	1450	1550	1650	1750	1850	1950	2050	2150	2250	2350	2450	2550	2650
Weight (kg) ^{Note 8}	35	37	39	41	43	45	47	48	50	52	54	56	58	60	62	64	66	68	70	72	74

N18D: Horizontal installation / Optional Cable carrier specification



N18D: Wall installation / Standard Cable carrier specification



N18D: Wall installation / Optional Cable carrier specification

